


DETAILS:



Acrylic Frames for Photo or Info/Poster Inserts / Rod Suspended

1. Acrylic frames used with vertical rod system are supplied as a set with 1/8" thick "clear" acrylic panel for backing and 1/8" thick "non-glare" acrylic panel for use as front cover. Panels are drilled for M4 studs. Holes are drilled for use with 14" rod centers.

2. Rods are mounted onto the wall with WM11-10 supports. P01 decorative support plates are optional.

3. Join three of the R1500-10 threaded rods together to create a 177" long rod. Use REC-10 end caps for rod-end finishing if necessary, otherwise cut rods and finish at support level.

4. Use RS13-10 supports to mount the acrylic info/poster frames to rods spacing them equally.

5. Inserts are mounted in between the two pieces of acrylic and fixed in place with low-tack (*3MTM 9415PC Removable Repositionable*) double sided adhesive tape.

Note: Non-glare (non-reflective) acrylic front cover helps to reduce the glare and provides a mild protection against harmful UV rays.

CL 1/4"

NG

1/8"



Nova Display Systems, Inc. 875 Wilson St., Ste. A-B Eugene, OR 97402 541.505.7450 541.505.9919 fax sales@novadisplay.com www.novadisplaysystems.com

Wall Display Concept

ID: DC2608

Title: Recognition Wall Display

Display Size: 52"H x 177"W

Wall Size Requirements: 16 FT (192 IN) Wide

Wall Install Template

ID: DC2608-WT

Note: Dimensions on the drawing display hardware mounting points on the wall. These are suggested dimensions and can be slightly modified to accommodate for your own wall specifics.

Note: This drawing is the property of Nova Display Systems and is not to be reproduced or copied in whole or in part. It is only to be used for the project and site specifically identified herein and is not to be used on any other projects, or for the purpose of manufacturing and reproduction. It is to be returned upon request.

Sheet:

Page: 1 of 1 Scale: n/a